

ORTA

Available in two different finishings, polished and mat surface.

The Orta gives a new charming look in a full aniline leather with a vintage visual appeal brought to a specific treatment that gives a veined and irregular surface.

Custom Colors Available

CHARACTERISTICS

Size
2 - 2,5 mq/20-26 sf

Thickness
0,9-1,1 mm

Raw material origin
European Bovine

Type of tannage
Chrome

Dyeing
Aniline

Finishing
Wax

PHYSICAL TEST

Rubbing resistance
≥3 gray scale (dry) 100 cycles
≥3 gray scale (wet) 20 cycles

Flex cracking
50.000 cycles (no cracking)

Light fastness
> 3 (blue scale)

LEATHER COMPLIANT TO

Cigarette test (BS 5852-1/79) – Match test

Cigarette test NFPA 260: 2003

IMO 652

IMVSS302

FS191 Method 5903 – Port Authority of NY & NJ

California TB 117 Section E

COMPLIANT ON REQUEST

FAR 25.853 (a)

FAR 25.853 (b)

UNI VF 9175 class1

IMO 653

BS 6853

DIN 5510

FS 191 Method 5903

Boston fire code BFD-IX-1

This leather is produced in conformity with REACH regulation

APPLICATIONS




AVAILABLE TREATMENTS

H2O 1

ACOUSTIC


FIRST CLASS




OT 001




OT 002



OT 003




OT 004




OT 005




OT 006




OT 007




OT 008




OT 009




OT 010




OT 011




OT 012




OT 013




OT 014




OT 015




OT 016




OT 017




OT 018




OT 019




OT 020




OT 021




OT 022




OT 023




OT 024




OT 025



OT 026




OT 027




OT 028


AVAILABLE
EMBOSSED




A




B




C




D




E




F




G




H




I




L




M



N




O



P



Q



R



S



T



U



W




X

The standard placement of the plate are shown in the diagram below.


HALF HIDE
Average size 1,8-2,2 mq / 20-25sf

PLATE
Plate size: 1000X1300 mm / 40X50 inch


OPTION 11




OPTION 12



OPTION 13



OPTION 14



The matchlines could be visible. Please verify the plate positioning prior to place an order.

MAINTENANCE ANILINE AND NUBUCK

- Avoid placing leather in direct sun
- Keep the leather away from direct heat
- Dust regularly with a soft and dry cloth
- Spots can be cleaned with a lightly damp cloth and mild soap
- Dry immediately after the treatment
- Do not rub. Use a light circular motion working toward the centre of the stain

CLEANING ANILINE AND NUBUCK

The following guidelines will help you to maintain the beauty of nubuck or aniline without destroying any of the natural characteristics:

Dry carefully the area , and use one of the following methods.

Pre-testing on a hidden area.

Light cleaner

4Nubuck Foglizzo Light Cleaner will clean most stains and soiling from Nabuck leather. It is water based product that penetrates into the surface to clean without harming your Nabuck Leather.

Spray cream

4Nubuck Foglizzo Spray Cream will provide excellent protection for your Nubuck and Suede leathers against oil and water based spills.

Power Cleaner

4Nubuck Foglizzo Power Cleaner efficiently removes surplus fat and oil spots on Nubuck leather. It is to be used for oil based stains. Try first to clean the stain with 4Nubuck Foglizzo Cleaning Cloth and 4Nubuck Foglizzo Light Cleaner. If this is not successful, use this product.